

UTC-300P-R

RFID Reader for UTC-300 Series



Specifications

Interface	USB
Cable Length	50cm
Frequency	13.56 MHz
RFID R/W Mode	Support ISO15693, ISO14443A/B, Felica, Mifare Ultralight
NFC	Support NFCIP-1 (ISO 18092), NFCIP-2 (ISO/IEC21481)
NFC Card Mode	Simulates ISO14443A/B mode
NFC R/W Mode	Support Type 1/2/3/4
OS Support	Windows XP/7/8
Dimensions	101 x 37 x 25 mm
Operating Temperature	0 ~ 40° C

Packing List

Description	Quantity
RFID Reader Unit	1
Bracket	1
Screw	2
Installation Guide	1

Ordering Information

P/N	Description
UTC-300P-R10E	RFID Reader, White, for UTC-315
UTC-300P-R11E	RFID Reader, Black, for UTC-315
UTC-300P-R20E	RFID Reader, White, for UTC-318
UTC-300P-R21E	RFID Reader, Black, for UTC-318

UTC-300P-S

Smart Card Reader for UTC-300 Series



Specifications

Interface	USB
Cable Length	50cm
Card Acceptor/ Reliability	Friction Type (ID-1) , 200,000 cycles
International Standard	Comply with PC/SC 1.0 standard and EMV L1
Compliant IC Card Standard	CPU Card: Comply with ISO7816-1,2,3,T=1 and T=0 protocol Memory Card: Synchronous 2-line, 3-line and I ² C interface
LED	Dual color LED indicator
OS Support	Windows XP/7/8
Dimensions	101 x 37 x 25 mm
Operating Temperature	0 ~ 40° C

Packing List

Description	Quantity
Smart Card Reader Unit	1
Bracket	1
Screw	2
Installation Guide	1

Ordering Information

P/N	Description
UTC-300P-S10E	Smart Card Reader, White, for UTC-315
UTC-300P-S11E	Smart Card Reader, Black, for UTC-315
UTC-300P-S20E	Smart Card Reader, White, for UTC-318
UTC-300P-S21E	Smart Card Reader, Black, for UTC-318

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[UTC-300P-R20E](#) [UTC-300P-R21E](#)