


KN-v3-M02-3 cable

3 m pair cable with soldered (tinned) end of wires




Connector pin-out, view into the router
(rear view of cable connector)


USED COMPONENTS:

- 2x 649 006 137 22 (4.20mm Female Terminal WR-MPC4)
 1x 649 002 113 322 (4.20mm Female Dual Row Plug WR-MPC4)
 1x VM03V2H-H 2x0,50 BK/RD cable length of 3m
 1x Shrinkable tube (ca. 1cm long)

PACKAGE:

The outer diameter must not exceed 95 mm.
The cable is needed to tie using 1–2 wires.
Connector is placed inside.
The cable is wrapped in a plastic bag
of a maximum size 100x130 mm



4					
3					
2					
1	Přidáno balení, odstraněna ver. 1m	P. Hanuš 1.8.2016	M. Počtýnský 1.8.2016	P. Kopecký 1.8.2016	
0	VÝCHOZÍ DOKUMENT	P. Hanuš 14.11.2014	E. Doskočil 14.11.2014	P. Kopecký 14.11.2014	
Rev.	Description of changes	Drawn Date Signature	Checked Date Signature	Approved Date Signature	
Length unit: mm		Assembly drawing:		 <p>Conel s.r.o., Sokolská 71 562 04 Ústí n. Orlicí III tel./fax: 465 521 020, 021 mobile-exchange: 603 872 287 E-mail: info@conel.cz http://www.conel.cz/</p>	
Accuracy:		Old drawing:			
Tolerance:		Commission:			
Scale:	Format: A4	File: VKA-2014-03-1.dwg			
Drawing name: KN-v3-MO2 cable			Drawing number: VKA-2014-03-1		Sheet: 1 Num. of sheets: 2
Issue No.:					
This document is know-how of the CONEL Ltd company Usti n/O. It may not be handed over to third person or abuse without permit.					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-KN-v3-MO2-3](#)