


KN-v3-M02-3 cable



3 m pair cable with soldered (tinned) end of wires

Soldered (tinned)
end of wires (1 cm)



1 BLACK GND(-)
2 RED VCC(+)

Connector pin-out, view into the router
(rear view of cable connector)



USED COMPONENTS:

2x 649 006 137 22 (4,20 mm Female Terminal WR-MPC4);
1x 649 002 113 322 (4,20 mm Female Dual Row Plug WR-MPC4);
1x VM03V2H-H 2x0,50 BK/RD cable length of 3 m;
1x Shrinkable tube (ca. 1 cm long).

PACKAGE:

The outer diameter must not exceed 95 mm;
The cable is needed to tie using 1-2 wires;
Connector is placed inside;
The cable is wrapped in a plastic bag of a maximum size 100x130 mm.

0	INITIAL DESIGN	Petr Baňanka	29.03.2021					
Rev.	Description of changes	Created	Date	Verified	Date	Approved	Date	
Scale:	1:1	Weight:	g	ADVANTECH Advantech Czech s.r.o. Sokolská 71, Kerhartice 562 04 Ústí nad Orlicí phone/fax: 465 524 421 mobile: 603 872 287 E-mail: cellular.info@advantech.cz http: // www.advantech.cz /				
Tolerance:	ISO 2768-mk	Material:						
Length units:	mm							
File name:	VKA-2014-03-1_KN-v3-M02 cable.slddrw							
Assembly drawing:								
Drawing name:	KN-v3-M02 cable		Drawing number:	VKA-2014-03-1		Sheet:	1	
						Total sheets:	1	
							A4	

This doc. is the intellectual property of Advantech Czech s.r.o. Ústí n / O. Without the written consent of the comp.it isn't be handed over to a third party or otherwise misused.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-KN-v3-MO2-3](#)