



# 96MPI3S-2.7-4M11T

Intel® Core™ i3-6100TE Processor (4M Cache, 2.70 GHz)



### Features:

- Intel I3-6300TE Processor
- 2 Cores
- 4MB smart cache
- Processor Base Frequency 2.6 GHz
- FCLGA1151 Socket Type
- Thermal Design Power 35W
- Intel HD Graphics 530
- Support DDR4-1866/2133, DDR3L-1333/1600 @ 1.35V



## Specifications

Advantech PN	96MPI3S-2.7-4M11T
Intel Ordering Code	CM8066201938603
Intel Launch Date	Q4 / 2015
Code Name	Skylake
SPEC Code	SR2LS
Processor Number	i3-6100TE
# of Cores	2
# of Threads	4
Cache	4MB
Clock Speed	2.7GHz
FSB (Front Side Bus)	N/A
Tech. in Nanometer	14nm
Max Design Power	35W

Direct Media Interface	8 GT/s
Socket Type	FCLGA1151
Max Memory Size	64GB
Tcase	N/A
Memory Type	DDR4-1866/2133, DDR3L-1333/1600 @ 1.35V
Intel® Graphic Processor	Intel HD Graphics 530
Graphic Base Frequency	350MHz
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHs	YES
Compatible Chipset	H170, H110, Z170, Q170, Q150, B150

## Compatible Motherboard

Model Number	Description

[Learn more on PAPS Website](#)

**ADVANTECH** Peripheral Allied Procurement Services –Your Ultimate Sourcing Partner–

All product specification and compatible chipset are subject to change without notice.

Last updated: 27-APR-2016  
Rev. 2.0

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPI3S-2.7-4M11T](#)