

96MPI3-3.7-4M10T



Intel® Core™ i3-4360 Processor (4M Cache, 3.70 GHz)



Features:

- Intel I3-4360 Processor
- 2 Cores
- 4MB smart cache
- Clock Speed 3.7 GHz
- FCLGA1150 Socket Type
- Max Power Design 54W
- Intel HD Graphics 4600
- Support DDR3- 1333/1600



Specifications

Advantech PN	96MPI3-3.7-4M10T
Intel Ordering Code	CM8064601482461
Intel Launch Date	Q2 / 2014
Code Name	Haswell
SPEC Code	SR1PC
Processor Number	i3-4360
# of Cores	2
# of Threads	4
Cache	4MB
Clock Speed	3.7GHz
FSB (Front Side Bus)	N/A
Tech. in Nanometer	22nm
Max Design Power	54W

Direct Media Interface	5 GT/s
Socket Type	FCLGA1150
Max Memory Size	32GB
Tcase	72C
Memory Type	DDR3-1333/1600
Intel® Graphic Processor	Intel HD Graphics 4600
Graphic Base Frequency	350MHz
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHs	YES
Compatible Chipset	H87, Q87, Q85, Z87, H81, B85, Z97

Compatible Motherboard

Model Number	Description
AIMB-274 Series	Intel® Core™ i7/i5/i3 LGA 1150 Mini-ITX with VGA/DP/HDMI(DP)/LVDS(eDP), 2COM, Dual LAN, PCIe x16
AIMB-784 Series	Intel® 4th Generation Core Processor-based platform

[Learn more on PAPS Website](#)

ADVANTECH

Peripheral Allied Procurement Services

—Your Ultimate Sourcing Partner—

All product specification and compatible chipset are subject to change without notice.

Last updated: 23-Sep-2014

Rev. 1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPI3-3.7-4M10T](#)