

96MPPS-3.3-3M11T



Intel® Pentium® Processor G4400 (3M Cache, up to 3.30 GHz)



Features:

- Intel Pentium G4400 Processor
- 2 Cores
- 2MB cache
- 14NM
- 54W
- HD Graphics 510



Specifications

Advantech PN	96MPPS-3.3-3M11T
Intel Ordering Code	CM8066201927306
Intel Launch Date	Q3 / 2015
Code Name	Skylake
SPEC Code	SR2DC
Processor Number	G4400
# of Cores	2
# of Threads	2
Cache	3MB
Clock Speed	3.3GHz
FSB (Front Side Bus)	N/A
Tech. in Nanometer	14nm
Max Design Power	54W

Direct Media Interface	8 GT/s
Socket Type	FCLGA1151
Max Memory Size	64GB
Tcase	N/A
Memory Type	DDR4-1866/2133, DDR3L-1333/1600 @ 1.35V
Intel® Graphic Processor	HD Graphics 510
Graphic Base Frequency	350MHz
64-bits Support	YES
Package	Tray
Embedded Channel	YES
RoHs	YES
Compatible Chipset	H170, H110, Z170, Q170, Q150, B150

Compatible Motherboard

Model Number	Description
Learn more on PAPS Website	

ADVANTECH Peripheral Allied Procurement Services - Global Sourcing Local Supports -

All product specification and compatible chipset are subject to change without notice.

Last updated: 4-NOV-2015

Rev. 1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96MPPS-3.3-3M11T](#)