

IEC320-C13 (Aus)

Country of Origin : China
Operating Temperature : $0 \div 40$ [°C]
Length/cord : 1.8m / 3x0.75mm²
Approvals : SAA, VDE, KEMA-KEUR, CEBEC, DEMKO, Intertek, Nemko, NCS/FI, SEV, ÖVE, IMQ, NF

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 197 g / pc
	Box	0.56 x 0.36 x 0.20 [m]
		150 pcs / 1box
		G.W.: 26 kg / box



IEC320-C13 (Brazil)

Country of Origin : China
Operating Temperature : $0 \div 40$ [°C]
Length/cord : 1.8m / 3x0.75mm²
Approvals : TUV, VDE, KEMA-KEUR, CEBEC, DEMKO, Intertek, Nemko, ENEC/FI, SEV, ÖVE

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 158g / pc
	Box	0.36 x 0.20 x 0.55 [m]
		100pcs / 1box
		G.W.: 16.7 kg / box



IEC320-C13 (Swiss)

Country of Origin : China
Operating Temperature : $0 \div 40$ [°C]
Length/cord : 1.8m / 3x0.75mm²
Approvals : SEV

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 169g / pc
	Box	0.36 x 0.20 x 0.55 [m]
		100pcs / 1box
		G.W.: 19kg / box



IEC320-C13 (EU)

Country of Origin : China
Operating Temperature : $0 \div 40[^\circ\text{C}]$
Length/cord : 1.8m / 3x0.75mm²
Approvals : VDE, KEMA-KEUR, CEBEC, DEMKO, Intertek, Nemko, NCS/FI, ÖVE, IMQ, NF, SEV

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 185g / pc
	Box	0.55 x 0.36 x 0.20 [m]
		90pcs / 1box
		G.W.: 18.2 kg / box



IEC320-C13 (UK)

Country of Origin : China
Operating Temperature : $0 \div 40[^\circ\text{C}]$
Length/cord : 1.8m / 3x0.75mm²
Approvals : ASTA

Application	For Class I. Appliances	
Fuse	5A / 250V	
WEIGHT / PACKING	1pc	N.W.: 195g / pc
	Box	0.48 x 0.26 x 0.44 [m]
		75pcs / 1box
		G.W.: 12.5 kg / box



IEC320-C13 (UL)

Country of Origin : China
Operating Temperature : $0 \div 40[^\circ\text{C}]$
Length/cord : 1.8m / 3x0.75mm²
Approvals : UL

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 72g / pc
	Box	0.56 x 0.36 x 0.20 [m]
		125pcs / 1box
		G.W.: 12.5 kg / box



IEC320-C13 (C)

Country of Origin : China
Operating Temperature : $0 \div 40[^\circ\text{C}]$
Length/cord : 1.8m / 3x0.75mm²
Approvals : CCC

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 182g / pc
	Box	0.55 x 0.36 x 0.20 [m]
		90pcs / 1box
		G.W.: 18.2 kg / box



IEC320-C13 (AG)

Country of Origin : China
Operating Temperature : $0 \div 40[^\circ\text{C}]$
Length/cord : 1.8m / 3x0.75mm²
Approvals : IRAM, VDE, CEBEC, KEMA-KEUR, DEMKO, Intertek, Nemko, NCS/FI, ÖVE, IMQ, NF, SEV

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 179g / pc
	Box	0.55 x 0.36 x 0.20 [m]
		90pcs / 1box
		G.W.: 18.0 kg / box



IEC320-C13 (Italy)

Country of Origin : China
Operating Temperature : $0 \div 40[^\circ\text{C}]$
Length/cord : 1.8m / 3x0.75mm²
Approvals : VDE, KEMA-KEUR, CEBEC, DEMKO, Intertek, Nemko, ENEC/FI, SEV, ÖVE, IMQ, NF

Application	For Class I. Appliances	
WEIGHT / PACKING	1pc	N.W.: 158g / pc
	Box	0.36 x 0.20 x 0.55 [m]
		100pcs / 1box
		G.W.: 16.9 kg / box



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-PWRCORD-AUS](#)