


DATE	REV	ECN	APP'D. BY
02/26/18	A0	--	JC



Notes:

- Each cable assembly to be individually bagged.
- 50μ" Gold plating on contacts
- Cable Construction:
 - 28AWG Stranded
 - 4Pr, U/UTP, Type CMR
 - PVC Jacket
- Slimline Snagless Strain Relief
- 100% Transmission Tested for Performance

P/N Key:

BM-R6UxxxxF

UOM


F = Feet

Color

E = Blue
K = Black
N = Green

Length	
XXX	Feet
001	1
003	3
005	5
007	7
010	10
015	15

Wiring Map: 568B Standard




Example Parts Numbers

Feet		
P/N	Color	Length
BM-R6UE001F	Blue	1'
BM-R6UK010F	Black	10'
BM-R6UN015F	Green	15'

For Part Numbers Not Shown Follow Part Number Key Format



THIRD ANGLE PROJECTION			206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com	
				
DO NOT SCALE DRAWING		TITLE: Bel Patchcord Assembly, C6 U/UTP, 28 awg, CMR		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE				
DIMENSIONS: INCHES [METRIC]		THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE $\pm .005$ [0.13] ANGLES ARE $\pm 1^\circ$				
SHEET NO. 1 OF 1				
		DRN BY: TLS	DATE 02/26/18	
		APPD BY: JC	DATE 02/26/18	
		DWG NO. CT999173	REV. A0	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BM-R6UE007F](#) [BM-R6UE010F](#) [BM-R6UE003F](#) [BM-R6UE015F](#) [BM-R6UE001F](#) [BM-R6UE005F](#)