

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	CPMC8813-CUST	版本 Rev	02	日期 Rel'd Date	Jan16,12
-----------	---------------	-----------	----	------------------	----------

Description: BNC 3pc crimp plug RG223

Part No: CPMC8813

Application: For RG142,223,400,55 Cable

Crimp Tool: 24-9958P

Impedance: 50 Ohms

Frequency Range: 0-4 GHz

Material:

Body	Zinc Nickel plated
Contact	Brass Gold plated
Insulator	Teflon
Crimp sleeve	Brass Nickel plated
Coupling nut	Zinc Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000







DRAWING NO.

CPMC8813-CUST

REVISIONS

01	OFFICAL RELEASE					
	08-17-09	J	T	T		
02	DIMENSIONS: $\Phi 14.3 \pm 0.3$ WAS $\Phi 14.5$ $\Phi 6.6$ WAS $\Phi 6.4$ ADD CABLE STRIP DIMENSIONS					
	12-31-11	Y	Y	M		ECO-11-0270



DIM OUTLINE

CABLE STRIP DIMENSIONS

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		JEAN.JIN	08-17-09
X		CHECKED BY	DATE
X.X		TERRY.W	08-17-09
X.XX		APPROVED BY	DATE
X.XX		THOMAS	08-17-09
ANGLES		U/M	mm
			ϕ \square

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.



TITLE
BNC 3PC CRIMP PLUG RG223

SHEET 1 OF 1	DRAWING NO. CPMC8813-CUST	SIZE A
-----------------	------------------------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[CPMC-88-13](#)