


SCMS5D25

SMD POWER INDUCTORS





• Features

1. Magnetically shielded construction – Low EMI
2. Excellent Power Density
3. Engineered to Provide High Efficiency

ELECTRICAL CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (3) (A)	Temperature Current (4) (A)
SCMS5D25-R50	0.50	100KHZ	19m	4.9	5.60
SCMS5D25-R87	0.87	100KHZ	23m	3.6	5.00
SCMS5D25-1R2	1.2	100KHZ	26m	3.2	4.50
SCMS5D25-1R8	1.8	100KHZ	30m	2.5	3.60
SCMS5D25-2R2	2.2	100KHZ	34m	2.2	3.24
SCMS5D25-3R3	3.3	100KHZ	42m	1.8	2.46
SCMS5D25-4R7	4.7	100KHZ	56m	1.5	2.21
SCMS5D25-6R8	6.8	100KHZ	70m	1.25	1.98
SCMS5D25-8R2	8.2	100KHZ	90m	1.18	1.78
SCMS5D25-100	10	100KHZ	0.12	1.05	1.60
SCMS5D25-150	15	100KHZ	0.13	0.93	1.44
SCMS5D25-220	22	100KHZ	0.19	0.77	1.29
SCMS5D25-330	33	100KHZ	0.33	0.63	1.04
SCMS5D25-470	47	100KHZ	0.36	0.49	0.93
SCMS5D25-680	68	100KHZ	0.57	0.41	0.75
SCMS5D25-820	82	100KHZ	0.79	0.38	0.67
SCMS5D25-101	100	100KHZ	0.82	0.35	0.58
SCMS5D25-151	150	100KHZ	1.30	0.28	0.45
SCMS5D25-221	220	100KHZ	2.10	0.22	0.40
SCMS5D25-331	330	100KHZ	3.12	0.20	0.32
SCMS5D25-471	470	100KHZ	4.70	0.16	0.27
SCMS5D25-681	680	100KHZ	8.10	0.12	0.19
SCMS5D25-821	820	100KHZ	8.65	0.11	0.18
SCMS5D25-102	1000	100KHZ	9.72	0.10	0.17



(1). Inductance tolerance for 0.5uH~8.2uH: $\pm 30\%$, for 10uH~1000uH: $\pm 20\%$. Tested at 0.25V, 0ADC and 25°C

(2). DCR measured at 25°C.

(3). The DC current at which the inductance decreases by 30% from its initial value.

(4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SCMS5D25-821](#) [SCMS5D25-100](#) [SCMS5D25-6R8](#) [SCMS5D25-330](#) [SCMS5D25-820](#) [SCMS5D25-3R3](#)
[SCMS5D25-R87](#) [SCMS5D25-151](#) [SCMS5D25-470](#) [SCMS5D25-221](#) [SCMS5D25-8R2](#) [SCMS5D25-1R2](#) [SCMS5D25-](#)
[331](#) [SCMS5D25-1R8](#) [SCMS5D25-681](#) [SCMS5D25-102](#) [SCMS5D25-471](#) [SCMS5D25-2R2](#) [SCMS5D25-R50](#)
[SCMS5D25-220](#) [SCMS5D25-150](#) [SCMS5D25-101](#) [SCMS5D25-680](#) [SCMS5D25-4R7](#)