

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	25-7308	版本 Rev	01	日期 Rel'd Date	Dec6,12
-----------	---------	-----------	----	------------------	---------

Description: UHF MALE CRIMP TYPE RG59/U

Part No: 25-7308

Application: N/A

Crimp Tool: N/A

Impedance: 75 ohm

Frequency Range: 0~1 GHz

Material: Body Zinc
Insulator ABS
Contact Brass
Shell Zinc

RoHS Compliance: Yes

Technical Detail: N/A

DRAWING NO.
25-7308

REVISIONS

01

OFFICIAL RELEASE

11-07-12

Y

G



Y

G


M

L

Lin Ma

BY: YUGU HU
DATE: 11-07-12
REV: 01

DIM OUTLINE

RECOMMENDED CABLE
STRIPPING DIMENSIONS

CUSTOMER COPY



cinch
CONNECTIVITY SOLUTIONS
a bel group

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		YUGE HU	11-07-12
X		CHECKED BY	DATE
X.X		YUGE HU	11-07-12
X.XX		APPROVED BY	DATE
X.XX		LIN MA	11-07-12
ANGLES		U/M	MM
± 2°			

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

TITLE

UHF MALE CRIMP TYPE RG59/U

SHEET
1 OF 1

DRAWING NO.
25-7308

SIZE
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[25-7308](#)