

RED INDICATES ORIGINAL


DATA CONTAINED IN THIS DOCUMENT IS
 PROPRIETARY TO TROMPETER ELECTRONICS, INC.
 AND SHALL NOT BE DISCLOSED, COPIED OR USED
 FOR PROCUREMENT OR MANUFACTURE WITHOUT
 EXPRESS WRITTEN PERMISSION.

REVISONS			3100/3200	SH 1
REV	ED	DESCRIPTION	DWN	APPROVED
U	11688	ADDED NON-STANDARD OPTION NUMBER 25; SEE ECD	DKC	<i>Bmip</i>
				6/12/96

TABLE 1 STD JACKS ACCOMMODATED
J3, J3W, J3A, J3WA, J3D, J3WD, J3E-N, J3WE-N, J3C-N, J3WC-N, J5, J5W, J13-R, J13W-R, J13C-N-R, J13WC-N-R, J72, J72S-N, J72D, JJ-042, J14, J14W, J14C-N, J14WC-N, J14T-R, J14WT-R, J14M, J14WM, J14MT-R, J14WMT-R, J14A, J14WA, J15-N, J15W-N

SUFFIX NO	TABLE 2 NONSTANDARD OPTIONS
01	NO DS OR DS MTG HOLES
02	SUBST DS2 (.87W)
03	SUBST DS3 (.312W)
04	REAR MOUNT BACKBAR
05	OPTIONS 01 & 04
06	NO PAINT (NO TFS-2)
07	OPTIONS 01, 04 & 06
08	SEMIGLOSS ENAMEL TT- E-529C PER MIL-STD- 808/F-302, TYPE I CLR 24672/FED STD 595
09	CLR 1703B/FED STD 595
10	ONE DS1 ONLY
11	CLR 26329/FED STD 595
12	CL SLOTS EIA-310
13	OPTIONS 11 & 12
14	SUBST DS5 (.424 W)
15	OPTION 01 & PAINT TFS-2 EXCEPT CLR 26492/FED STD 595
16	OPTIONS 02 & 12
17	CLR 26622/FED STD 595
18	CLR 26440/FED STD 595
19	
20	MARK BACKBAR IAW TMS-3A
21	CLR 26556/FED STD 595
22	OPTIONS 02 & 21
23	CLR 24664/FED STD 595
24	CLR 27038/FED STD 595
25	CARDINAL CLR #62468 REF:RAL-7035

TABLE 3		
BASIC PART NO	BASIC MODEL NO	PANEL TYPE
3100	JS-48A	NONINSULATED
3200	JSI-48A	INSULATED



FOR OPTION 12, 13 AND 16 USE 850-0000-44

- .008 MAX ADDED PER PAINTED SURFACE
- STANDARD CONFIGURATION SHOWN, NONSTANDARD OPTION
SUFFIX ON PART NO MAY CHANGE OR ELIMINATE DIM
AND/OR FEATURES SHOWN

- PART IDENTIFICATION;

COMPLETE PART NO:

3100-J3

COMPLETE MODEL NO:

JS-48A/J3

00 SUFFIX STD PER TABLE 3
 SUBSTITUTE *01* OR *02* ETC FOR
 NONSTD OPTIONS PER TABLE 2

PANEL TYPE
 SEE TABLE 3

JACK TYPE ONLY IF REQD ON ASSY
 SEE TABLE 1, STD JACKS ACCOM*
 -101 IF PANEL ONLY
 -102 IF BACKBAR ONLY

QTY OF JACKS AND/OR MTG HOLES

- PANEL PER EIA-310

- STD FINISH, TFS-2: LIGHT GRAY SEMIGLOSS
 ENAMEL, MIL-E-15080B, TYPE III, CLASS 2
 COLOR NO 26307/FED-STD-595

- ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED .001 ±.003 .002 ±.010 .003 ±.010 ANG 1/2	TROMPETER ELECTRONICS, INC.	JS-48A/JSI-48A	
DWN DKC 8-11-88	MATERIAL CODE IDENT	DRAWING NO.	REV
CHK <i>Bm</i> 6-12-96	14949	3100/3200	U
ENGR <i>PS</i> 6/12/96	SCALE 1/2	DATE 7/24/78	SHEET 1 OF 2

NEXT ASSY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[JSI-48A](#)