

RED IS ORIGINAL

DISK # DWG SIZE
H 4 C








DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS, INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PRODUCTION OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISONS			3-0117	SH 1
REV	ED	DESCRIPTION	OWN	APPROVED
F	10049	PICTORIALLY CHANGED 1.00 FLARED SEALING SLEEVE TO STRAIGHT (1.25) LONG SEALING SLEEVE; GENERAL UPDATE	DKC	<i>Agg. Fd</i>
				12/15/92

TABLE 1			
DASH NO	MODEL NO	CENTER CONTACT/INTMD CONTACT TYPE	FIG NO
-1	BJ459ACFLP	SOCKET/PIN	1
-2	BJ459ACFLS	PIN/SOCKET	
-3	BJ459ACPP	SOCKET/PIN	
-4	BJ459ACPS	PIN/SOCKET	2
-5	BJ459ACRP	SOCKET/PIN	
-6	BJ459ACRS	PIN/SOCKET	3
-7	BJ459ACWP	SOCKET/PIN	
-8	BJ459ACWS	PIN/SOCKET	4

TABLE 2				
CABLE GROUP NO	CABLES ACCOMMODATED	A DIM	B DIA	C HEX
-201	M17/176-00002	1.365	.334	.255
-202	TWC-78-1, TROMPETER			
-203	TWC-124-1A, TROMPETER			
-204	10602 RAYCHEM			
-205	TWAC-78-1F2, TROMPETER			
-206	782600130, RAYCHEM			
-208	202-3927, MICRODOT			
-209	202-3942, MICRODOT			
-212	2524E0114, RAYCHEM			
-217	9C875TM24H, GRUMMAN			
-218	EPD221888, RAYCHEM			
-219	2526D1114, RAYCHEM			
-220	9C875RR1, GRUMMAN			
-221	10614 RAYCHEM			
-222	10613 RAYCHEM			
-223	HMS2-1149, HUGHES			

INCH	MM
.003	0.08
.0050	0.13
.010	0.25
.030	0.76
.047	1.19
.071	1.80
.156	3.96
.2400	6.10
.255	6.48
.274	6.96
.278	7.06
.330	8.38
.334	8.48
.335	8.51
.43	10.92
.4375	11.11
.707	17.96
1.25	31.75
1.365	34.67



SEALING SLEEVE & CRIMP BUSHING LOOSE WITH EACH CONNECTOR EXCEPT NOT USED ON -205, -208 & -223

6. EXAMPLE OF COMPLETE MODEL NO:
 BASIC MODEL NO (SEE TABLE 1) BJ459AC W P - 201
 CABLE GROUP NO (SEE TABLE 2)
 LUG POLARIZATION FL = 4-LUG, FIG 1
 P = 3-LUG, FIG 2
 R = 3-LUG, FIG 3
 W = 3-LUG, FIG 4
 CENTER & INTERMEDIATE CONTACT TYPE (SEE TABLE 1)

5. EXAMPLE OF COMPLETE PART NO:
 BASIC PART NO 3-0117 -1 -201
 DASH NO (SEE TABLE 2)
 LUG POLARIZATION, CENTER & INTERMEDIATE CONTACT TYPE: SEE TABLE 1

4. MAX PANEL THK .156

3. CONCENTRIC TWINAX 4 PIECE ASSY. FULL CRIMP NONINSULATED BULKHEAD MOUNT RECEPTACLE, SOCKET CENTER CONTACT AND PIN INTERMEDIATE CONTACT OR PIN CENTER CONTACT AND SOCKET INTERMEDIATE CONTACT

2. FINISH: TFS-1U (500 HOURS SALT SPRAY; NICKEL)

1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ±.03 .XXX ±.010 .XXXX ±.0050 ANGLE± 0° 30'	TROMPETER ELECTRONICS, INC.	BJ459ACFLP/FLS/PP/PB/PP/RS/WP/WS	
DWN DKC 12-2-92 CHK <i>Agg</i> 12/9/92 ENGR <i>Agg</i>	MATERIAL	CODE IDENT 14949	DRAWING NO. 3-0117
NEXT ASSY	APPR <i>Agg</i> 12/15/92	SCALE 2/1	DATE 5-20-87 SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[BJ459ACWP-201](#)