



DESCRIPTION: CAT5E MOLDED & BOOTED PATCH CABLE
 MODEL NUMBER: 73-779X-XXX
 APPLICATION: PATCH CABLE
 CRIMP TOOL: N/A
 IMPEDANCE: N/A
 FREQUENCY RANGE: N/A
 MATERIAL: PLUG RJ-45, GODL PLATED
 HOOD PVC
 CABLE UTP, 24 AWG, 4 TWISTED PAIRS, STRANDED
 BARE COPPER, UL ETL EIA/TIA-568B
 VERIFIED CATEGORY 5E

RoHS COMPLIANCE: YES
 TECHINCAL DETAIL: N/A





TABLE 1

MODEL NUMBER	LENGTH (FEET)	DESCRIPTION
73-779X-1	1	CAT5E MOLDED & BOOTED PATCH CABLE, 1FT
73-779X-1.5	1.5	CAT5E MOLDED & BOOTED PATCH CABLE, 1.5FT
73-779X-3	3	CAT5E MOLDED & BOOTED PATCH CABLE, 3FT
73-779X-5	5	CAT5E MOLDED & BOOTED PATCH CABLE, 5FT
73-779X-7	7	CAT5E MOLDED & BOOTED PATCH CABLE, 7FT
73-779X-10	10	CAT5E MOLDED & BOOTED PATCH CABLE, 10FT
73-779X-14	14	CAT5E MOLDED & BOOTED PATCH CABLE, 14FT
73-779X-25	25	CAT5E MOLDED & BOOTED PATCH CABLE, 25FT
73-779X-35	35	CAT5E MOLDED & BOOTED PATCH CABLE, 35FT
73-779X-50	50	CAT5E MOLDED & BOOTED PATCH CABLE, 50FT
73-779X-100	100	CAT5E MOLDED & BOOTED PATCH CABLE, 100FT

X=COLOR
 0=GRAY
 1=BLACK
 2=BLUE
 3=GREEN
 4=RED
 5=YELLOW
 6=WHITE
 7=ORANGE
 8=PINK
 9=VIOLET



This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	3RD ANGLE PROJECTION 	AIM-Cambridge	
	RoHS2 ☒ 2011/65/EU	Title: CAT5E MOLDED & BOOTED PATCH CABLE	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH -XX ±.02 -XXX ±.005 ANGLES ±2°	Model No. 73-779X-XXX	
	Size A	DO NOT SCALE DRAWING	Date: 2015/5/18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cinch Connectivity Solutions:

[73-7792-100](#) [73-7796-7](#) [73-7791-100](#) [73-7791-10](#) [73-7791-5](#) [73-7792-10](#) [73-7792-5](#) [73-7793-5](#) [73-7797-25](#) [73-7797-50](#) [73-7795-1](#)