



DATE	REV	ECN	APP'D. BY
11/06/19	A0	—	JME
12/04/19	A1	11483	ADB



PART NUMBER KEY



O/A Length Tolerance:


Metric	
0 ~ 200mm	±10mm
201 ~ 1000mm	±20mm
1001 ~ 1500mm	±25mm
1501 ~ 2100mm	±30mm
>2100mm	±40mm

Imperial	
0 ~ 1ft	±0.5in
2ft ~ 3ft	±0.75in
4ft ~ 7ft	±1.0in
> 7ft	±1.5in

NOTES:

1. EACH CABLE ASSEMBLY INDIVIDUALLY BAGGED
2. CONNECTOR (P1): DVI 19 MALE, GOLD PLATING ON CONTACTS, GOLD CONNECTOR, BLACK INSULATOR
3. CONNECTOR (P2): DVI 19 MALE, GOLD PLATING ON CONTACTS, GOLD CONNECTOR, BLACK INSULATOR
4. WIRE CONSTRUCTION: UL20276; BLACK JACKET, OD 0.287" [7.3 mm]
5. FERRITE CORE: 0.7 x 1.12 x 0.41", MOLDED BLACK PVC

WIRING MAP




TYPICAL PART NUMBERS	
PART NUMBER	LENGTH METERS [FEET]
BC-VDSK010M	1 [3.28]
BC-VDSK020M	2 [6.56]
BC-VDSK030M	3 [9.84]
BC-VDSK050M	5 [16.4]
FOR PART NUMBERS NOT SHOWN FOLLOW PART NUMBER KEY FORMAT	

RoHS



THIRD ANGLE PROJECTION




DO NOT SCALE DRAWING  
DRAWING IS SUBJECT TO  
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE ±.005 [0.13]  
ANGLES ARE ± 1°

SHEET NO. 1 OF 1



**bel**

206 Van Vorst Street  
Jersey City, NJ 07302  
+1 201 432 0463  
<http://www.belfuse.com>

TITLE: DVI-D SINGLE LINK TO DVI-D SINGLE LINK (18+1 TYP.)  
CABLE WITH FERRITE CORE

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON  
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF  
BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,  
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN  
CONSENT OF BEL FUSE, INC.

DRN BY: BTS	DATE 11/06/19
APPD BY: JME	DATE 11/06/19
DWG NO. CT999210	REV. A1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-VDSK010M](#) [BC-VDSK020M](#)