

5

4

3

2

1

DRAWING NO.			
32-1006-CUST(SEE TABLE I)			
REVISIONS			
01	OFFICIAL RELEASE		
	08-12-09	Y U T H	2009.09.08 09:28:26 Betty + 08 00

Description: See Table I

Part No: See Table I

Application: Unshielded Modular In-line Coupler
Cross Wired for Voice Applications

Crimp Tool: N/A

Impedance: N/A

Frequency Range: N/A



Material: Wire 26AWG,PVC,OD1.0mm,UL1061
Housing ABS,Color See Table I
Pin Phosphor Bronze,Copper Plated

RoHS Compliance: Yes

Technical Detail: N/A



受控 CONTROLLED DOCUMENT					
编号 P/N	30-1006-C UST	版本 Rev	01	日期 Rel'd Date	SEP 14,09




10.00
(.394 in)
16.7
(.657 in)

TABLE I

P/N	Description	Color
32-1006	RJ12 6P6C COUPLER X-WIRED,IV	Ivory
32-1006W	RJ12 6P6C COUPLER X-WIRED,WH	White

CUSTOMER COPY



PIN ASSIGNMENT

- J 1 J 2
- 2 5 YELLOW
- 3 4 GREEN
- 4 3 RED
- 5 2 BLACK

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY BETTY.YU		DATE 08-12-09		 Connectivity Solutions					
DECIMALS	mm	CHECKED BY BETTY.YU		DATE 08-12-09							
X	± 0.5	APPROVED BY THOMAS		DATE 08-12-09		TITLE RJ12 6P6C COUPLER X-WIRED,IV (SEE TABLE I)					
X.X	± 0.3										
X.XX	± 0.1										
ANGLES	± 0.5°	U/M mm									
THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.						SHEET 1 OF 1		DRAWING NO. 32-1006-CUST (SEE TABLE I)		SIZE A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[32-1006](#)