

5

4

3

2

1

D

C


B

A



Description: See Table I  
Part No: See Table I  
Application: Single port surface mount box  
Category 4 screw termination  
Bottom entry wiring  
Crimp Tool: N/A  
Impedance: N/A  
Frequency Range: N/A  
Material: Wire 24-26AWG,Solid wire  
Housing ABS,Color See Table I  
Pin Phosphor Bronze,Copper Plated  
RoHS Compliance: Yes  
Technical Detail: N/A

受控 CONTROLLED DOCUMENT					
编号 P/N	32-2034	版本 Rev	01	日期 Rel'd Date	DEC 17,09



### DIM OUTLINE

TABLE I

Part Number	Description	Color
32-2034	SURFACE MT JACK, 4COND,IVORY	IVORY
32-2034W	SURFACE MT JACK, 4COND,WHITE	WHITE
32-2036	SURFACE MT JACK, 6COND,IVORY	IVORY
32-2036W	SURFACE MT JACK, 6COND,WHITE	WHITE
32-2038	SURFACE MT JACK, 8COND,IVORY	IVORY
32-2038W	SURFACE MT JACK, 8COND,WHITE	WHITE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	LINDA.WU	11-19-09
X	± 0.5	CHECKED BY	DATE
X.X	± 0.3	LINDA.WU	11-19-09
X.XX	± 0.1	APPROVED BY	DATE
ANGLES	± 0.5°	THOMAS	11-19-09
		U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,  
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

DRAWING NO.  
32-2034-CUST(SEE TABLE I)

### REVISIONS

01	OFFICIAL RELEASE				Betty	2009.12.14 10:29:08 +08'00'
	11-19-09	L	L	T H		

CUSTOMER COPY



Connectivity  
Solutions

TITLE  
SURFACE MT JACK, 4COND,  
IVROY (SEE TABLE I)

SHEET 1 OF 1	DRAWING NO. 32-2034-CUST (SEE TABLE I)	SIZE A
-----------------	--	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[32-2036](#)