


TABLE 1	
DASH NO	DESCRIPTION
-1	CAP (NO CHAIN)
-2	CAP WITH 2.5 BRASS CHAIN
-3	CAP WITH 2.5 NYLON CHAIN
-4	CAP WITH 3.0 BRASS CHAIN
-5	CAP WITH 3.0 NYLON CHAIN
-6	CAP WITH 6.0 BRASS CHAIN
-7	CAP WITH 6.0 NYLON CHAIN
-8	CAP WITH 4.0 BRASS CHAIN
-9	CAP WITH 4.0 NYLON CHAIN
-10	CAP WITH 10.0 BRASS CHAIN
-11	CAP WITH 10.0 NYLON CHAIN
-12	CAP WITH 2.5 INCH SST ROPE
-13	CAP WITH 3.0 INCH SST ROPE
-14	CAP WITH 6.0 INCH SST ROPE
-15	CAP WITH 4.0 INCH SST ROPE
-16	CAP WITH 7.0 INCH SST ROPE
-17	CAP WITH 4.5 INCH SST ROPE

TABLE 2	
MODEL NO	TYPE
RFI85	2-LUG
RFI853	3-LUG
RFI385	THREAD

TABLE 3				
DASH NO	"A" DIA	"B" DIA	"C" DIM	"D" DIM
-D1	.755	.875	1.191	.513
-D2	.630	.750	1.066	.450
-D3	.505	.625	.941	.388
-D4	.439	.562	.878	.355
-D5	.380	.500	.816	.325
-D6	.317	.437	.753	.295
-D7	.281	.406	.722	.278
-D8	.610	.750	1.066	.450
-D9	.567	.687	1.003	.419
-D08	.330	.450	.766	.300
-D10	.192	.312	.628	.231

REV		ED		REVISIONS		305-0137		SH	IC
REV		ED		DESCRIPTION		DWN		APPROVED	
F		13357		ADDED -12-01 THRU -17-008, -112-01 THRU -117-008, -812-01 THRU -817-008, AND ITEM 16 TO BOM FOR SST WITH D-LUG B-3285-1 AND 2; ADDED VIEW FOR SST ROPE & D-LUG; CHANGED NOTE 4; 56 ±.03 WAS .560 ±.030; GENERAL UPDATE; SEE ECO		OKC		[Signature]	



4. EXAMPLE OF COMPLETE MODEL NO: RFI85-2-01

BASIC MODEL NO: RFI85-2-01

CHAIN/ROPE MATL AND LENGTH (SEE TABLE 1)

BULKHEAD JACK MOUNTING LUG (OPTIONAL)

3. MALE "C" STYLE DUST CAP
2. FINISH: NICKEL
1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
10, UNLESS SPECIFIED	TROMPETER ELECTRONICS, INC.	RFI 85/853/385	
10X ±.005			
300002			
ANALYSIS			
DWN	13-21-00	MATERIAL	CODE IDENT
CHK	14949	14949	305-0137
ENGR	14-14-73	SCALE 2/1	DATE 11-14-73
APP	14-14-73	SHEET	1C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[RFI385-13-D1](#)