


B

A

B


A

DATE	REV	ECN	APP'D. BY
10/20/20	A0	RELEASED	ADB
-	-	-	-




NOTES:

1. COMPLIANT WITH DISPLAYPORT 1.4 SPECIFICATION.
2. CONNECTOR COMPONENTS:  
TRANSPARENT DUST COVER  
INSIDE MOLDING: LDPE  
STRAIN RELIEF: 45P PVC, BLACK  
OUTSIDE MOLDING: ABS, BLACK  
SHELL PLATING: GOLD FLASH  
CONTACT: GOLD PLATING  
CABLE: DP1.4  
[27AWG(7/0.14TC)+EAM]\*5P+27AWG(7/0.14TC)\*4C+AEB(16/10/0.12 85%AL)  
OD: 0.29 [7.3] COLOR: BLACK  
CABLE PRINTING: DISPLAYPORT CABLE E342987 AWM STYLE 20276 80°C 30V VW-1
3. ELECTRICAL TESTING:  
100% OPEN & SHORT & CONTINUITY WIRE TEST  
CONTACT RESISTANCE: 3 OHM MAX.  
INSULATION RESISTANCE: 10M OHM MIN.  
HI-POT:100V DC/10ms
4. PACKAGING:  
ONE CABLE PER BAG




PIN ASSIGNMENT



P/N	LENGTH
BC-4D4D010F	120 [3050]

THIRD ANGLE PROJECTION



DO NOT SCALE DRAWING  
DRAWING IS SUBJECT TO  
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE ±.005 [0.13]  
ANGLES ARE ± 1°

SHEET NO. 1 OF 1



TITLE: DISPLAY PORT 1.4 CABLE, MALE TO MALE, 10 FEET

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON  
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF  
BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,  
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN  
CONSENT OF BEL FUSE, INC.

206 Van Vorst Street  
Jersey City, NJ 07302  
+1 201 432 0463  
<http://www.belfuse.com>

DRN BY: JE	DATE 10/07/20
APPD BY: ADB	DATE 10/20/20
DWG NO. CT999227	REV. A0



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-4D4D010F](#)