




B

B




NOTES:

1. COMPLIANT WITH DISPLAYPORT 1.4 SPECIFICATION.
2. CONNECTOR COMPONENTS:
TRANSPARENT DUST COVER
INSIDE MOLDING: LDPE
STRAIN RELIEF: 45P PVC, BLACK
OUTSIDE MOLDING: ABS, BLACK
SHELL PLATING: GOLD FLASH
CONTACT: GOLD PLATING
CABLE: DP1.4
[26AWG(7/0.16TC)+EAM]*5P+26AWG(7/0.16TC)*4C+AEB(16/110.12 85%AL)
OD: 0.33 [8.5] COLOR: BLACK
CABLE PRINTING: DISPLAYPORT CABLE E342987 AWM STYLE 20276 80°C 30V VW-1
3. ELECTRICAL TESTING:
100% OPEN & SHORT & CONTINUITY WIRE TEST
CONTACT RESISTANCE: 5 OHM MAX.
INSULATION RESISTANCE: 10M OHM MIN.
HI-POT:100V DC/10ms
4. PACKAGING:
ONE CABLE PER BAG



P/N	LENGTH
BC-4D4D015F	180 [4575]



THIRD ANGLE PROJECTION				206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com	
DO NOT SCALE DRAWING DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE		TITLE: DISPLAY PORT 1.4 CABLE, MALE TO MALE, 15 FEET			
DIMENSIONS: INCHES [METRIC]		THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.		DRN BY: JE	DATE 10/07/20
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°				APPD BY: ADB	DATE 10/20/20
SHEET NO. 1 OF 1				DWG NO. CT999228	REV. A0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-4D4D015F](#)