


REV	ECO	DATE
001	58770	08/23/2023



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIALS & FINISH:

- 1.1 BODY & INSERT: PASSIVATED STAINLESS STEEL
- 1.2 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
- 1.3 INSULATOR: PEEK

2. SPECIFICATIONS:

- 2.1 FREQUENCY RANGE: DC-40 GHz
- 2.2 IMPEDANCE: 50 OHMS NOMINAL
- 2.3 VSWR (MAX): 1.25:1
- 2.4 OPERATING TEMPERATURE: -65°C TO 85°C

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018	Model No:	CGM-1400-FF-29M-02		MIDWEST MICROW AVE	
	RoHS2	☒	2015/863/EU	Cage Code	34078
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	.XX ±.02	.XXX ±.010	ENGINEER:	R. BRENDAL
	ANGLES ±2°	Date:	09/05/2023	Size	A
Title:			2.92MM FEMALE TO FEMALE ADAPTOR		
Drawing No.			CGM-1400-FF-29M-02-01		
REV.			001		
DO NOT SCALE DRAWING			Workmanship Std: Sheet 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[CGM-1400-FF-29M-02](#)