


REV	ECO	DATE
001	58768	08/23/2023



NOTES: UNLESS OTHERWISE SPECIFIED

# 1. MATERIALS & FINISH:

- 1.1 BODY & INSERT: PASSIVATED STAINLESS STEEL
- 1.2 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
- 1.3 INSULATOR: PEEK

# 2. SPECIFICATIONS:

- 2.1 FREQUENCY RANGE: DC-40 GHz
- 2.2 IMPEDANCE: 50 OHMS NOMINAL
- 2.3 VSWR (MAX): 1.25:1
- 2.4 OPERATING TEMPERATURE: -65°C TO 85°C

<p>NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018</p>	Model No:	CGM-1400-MM-29M-02		MIDWEST MICROWAVE	
	RoHS2	2015/863/EU	Cage Code	34078	Title: 2.92MM MALE TO MALE ADAPTOR
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	3RD ANGLE PROJECTION	ENGINEER:	R. BRENDAL	Drawing No.
	.XX ±.02 .XXX ±.010 ANGLES ±2°	Date:	09/05/2023	CGM-1400-MM-29M-02-01	REV. 001
Size A		DO NOT SCALE DRAWING	Workmanship Std:	Sheet	1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[CGM-1400-MM-29M-02](#)