


**Electrical Characteristics**  
Nominal Impedance: 50 ohms  
Frequency Range: DC to 2.5 GHz  
Operating Voltage (rms): 335 V maximum at sea level

**Mechanical Characteristics**  
Mating Cycles: 500 cycles minimum

**Environmental Characteristics**  
Temperature Range: -55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated
2	Insulator	POM
3	Contact	Brass, gold plated

First Issue	SN	1	11 Feb 03
DESCRIPTION OF REVISION	APPVD	ISS	DATE

 <div>Cinch Connectivity Solutions 7-13 Russell Way, Widford Industrial Estate, Chelmsford, Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515 Fax: +44 (0) 1245 358938</div>	SCALE: Not To Scale	DRAWN BY:	S Nash	TITLE:  BNC Plug to Mini UHF Jack	PART NUMBER:  VA303
	DIMENSIONS: mm	CHECKED BY:	P Couzens		
	TOLERANCES: ± 0.2mm unless otherwise stated	APPROVED BY:	P Couzens		PAGE: 1 of 1
		DATE:	11 Feb 03		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[VA303](#)