



DATE	REV	ECN	APP'D. BY
11/5/20	A0	Released	AB

ISOMETRIC VIEW



JACK HOUSING LEFT



JACK HOUSING RIGHT



TRANSMISSION PERFORMANCE  
Meet all requirement specified in channel requirement of:  
ISO/IEC 11801 , Class E<sub>A</sub>  
ANSI/TIA-568-C.2, Category 6A

ELECTRICAL  
Electrical Insulation Resistance : 500 MΩ min. @ 100V d.c  
Dielectric Withstanding Voltage : 1000V d.c. or a.c. Peak Contact to Contact @ 60Hz for 1 minute

MECHANICAL  
Insertion / Extraction Life : 750 Cycles Minimum

PHYSICAL  
Housing : High-Impact, Flame-Retardant Plastic, UL 94V-0  
Spring Wire : Phosphor Bronze Alloy Plated With 50 micro-inch of Gold

ASSEMBLY DIMENSION





COMPONENTS

ITEM	PART NAME	Q'TY
3	INSERT MODULE	2
2	JACK HOUSING LEFT	1
1	JACK HOUSING RIGHT	1

SS-82020-001

PART NUMBER

THIRD ANGLE PROJECTION



206 Van Vorst Street  
Jersey City, NJ 07302  
+1 201 432 0463  
<http://www.belfuse.com>

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: METRIC

UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE ±0.2  
ANGLES ARE ± 1°

SHEET NO. 1 OF 1

TITLE:

CAT 6A UNSHIELDED KEYSTONE COUPLER JACK

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

DRN BY: JE	DATE 10/28/20
APPD BY: AB	DATE 11/5/20
DWG NO. CT820037	REV. A0

RoHS  
2002/95/EC





# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SS-82020-001](#)