



DATE	REV	ECN	APP'D. BY
5/29/19	A0	RELEASED	—
10/15/20	A1	11639	JE





NOTES:

1. COMPLIANT WITH DISPLAYPORT 1.1 SPECIFICATION.
2. CONNECTOR COMPONENTS:
TRANSPARENT DUST COVER
INSIDE MOLDING: PE
STRAIN RELIEF MOLDING: 45P PVC, BLACK
OUTSIDE MOLDING: ABS, WHITE
SHELL PLATING: GOLD FLASH
CONTACT: GOLD PLATING
DISPLAY PORT UL20276 [32AWG(7/0.08TC)*1PR+EAM)*5
+32AWG(7/0.08TC)*5C+D(BC)+AB 85% (16/7/0.12AL)
OD: 0.19 [4.8] COLOR: WHITE
3. ELECTRICAL TESTING:
100% OPEN & SHORT & CONTINUITY WIRE TEST
CONTACT RESISTANCE: 2 OHM(MAX)
INSULATION RESISTANCE: 10M OHM(MIN)
HI-POT TEST: DC 100V/10ms
4. PACKAGING
ONE CABLE PER BAG



P/N	LENGTH
BC-DM003F	36±1.2 [915±30]
BC-DM006F	72±1.2 [1830±30]
BC-DM010F	120±1.6 [3050±40]



THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°

SHEET NO. 1 OF 1

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

TITLE: MINI DISPLAY PORT MALE TO DISPLAY PORT MALE CABLE

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

DRN BY: JMM	DATE 05/16/19
APPD BY: ADB	DATE 05/29/19
DWG NO. CT999193	REV. A1

ASSEMBLY FORMAT REV. 6/3/05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-DM003F](#) [BC-DM006F](#) [BC-DM010F](#)