


• Features

1. Open frame construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

CHARACTERISTICS

Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (3) (A)	Temperature Current (4) (A)
SC3DF-1R0	1.0	100KHZ	72m	1.34	2.90
SC3DF-1R5	1.5	100KHZ	84m	1.22	2.60
SC3DF-2R2	2.2	100KHZ	108m	1.08	2.30
SC3DF-3R3	3.3	100KHZ	134m	0.97	2.00
SC3DF-4R7	4.7	100KHZ	160m	0.91	1.80
SC3DF-6R8	6.8	100KHZ	197m	0.79	1.50
SC3DF-100	10	100KHZ	330m	0.63	1.10
SC3DF-120	12	100KHZ	350m	0.59	1.00
SC3DF-150	15	100KHZ	400m	0.56	0.92
SC3DF-180	18	100KHZ	450m	0.51	0.88
SC3DF-220	22	100KHZ	534m	0.47	0.86
SC3DF-270	27	100KHZ	618m	0.43	0.80
SC3DF-330	33	100KHZ	903m	0.37	0.72
SC3DF-390	39	100KHZ	1.01	0.34	0.62
SC3DF-470	47	100KHZ	1.36	0.29	0.56
SC3DF-560	56	100KHZ	1.52	0.28	0.52
SC3DF-680	68	100KHZ	1.71	0.26	0.48
SC3DF-820	82	100KHZ	2.31	0.22	0.43
SC3DF-101	100	100KHZ	2.64	0.21	0.40
SC3DF-121	120	100KHZ	3.50	0.19	0.36
SC3DF-151	150	100KHZ	4.13	0.17	0.33
SC3DF-181	180	100KHZ	4.53	0.16	0.30
SC3DF-221	220	100KHZ	6.65	0.13	0.27
SC3DF-271	270	100KHZ	7.52	0.12	0.24



(1). Inductance tolerance for 1.0uH~6.8uH: $\pm 30\%$, for 10uH~270uH: $\pm 20\%$. Tested at 0.25V, 0ADC and 25°C.

(2). DCR measured at 25°C.

(3). The DC current at which the inductance decreases by 10% from its initial value.

(4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.



belfuse.com/signal

© 2019 Signal Transformer –Specification subject to change without notice. 12.19

128 Atlantic Avenue, Lynbrook, NY 11563
Toll Free 866-239-5777 • Tel 516-239-5777 • Fax 516-239-7208
Sales@signaltransformer.com • techhelp@signaltransformer.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SC3DF-150](#) [SC3DF-330](#) [SC3DF-1R0](#) [SC3DF-221](#) [SC3DF-180](#) [SC3DF-270](#) [SC3DF-4R7](#) [SC3DF-181](#) [SC3DF-1R5](#) [SC3DF-121](#) [SC3DF-100](#) [SC3DF-820](#) [SC3DF-560](#) [SC3DF-680](#) [SC3DF-151](#) [SC3DF-6R8](#) [SC3DF-220](#) [SC3DF-390](#) [SC3DF-120](#) [SC3DF-271](#) [SC3DF-101](#) [SC3DF-3R3](#) [SC3DF-2R2](#) [SC3DF-470](#)