


SCB75C

SMD POWER INDUCTORS





• Features

1. Magnetically shielded construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

ELECTRICAL CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (A) (3)	Temperature Current (A) (4)
SCB75C-1R0	1.0	1KHZ	23m	2.88	7.00
SCB75C-1R5	1.5	1KHZ	27m	2.61	6.30
SCB75C-2R2	2.2	1KHZ	30m	2.46	4.84
SCB75C-3R3	3.3	1KHZ	35m	2.28	3.80
SCB75C-4R7	4.7	1KHZ	41m	2.08	3.42
SCB75C-6R8	6.8	1KHZ	47m	1.94	3.07
SCB75C-100	10	1KHZ	50m	1.68	2.60
SCB75C-120	12	1KHZ	70m	1.54	2.34
SCB75C-150	15	1KHZ	80m	1.39	2.10
SCB75C-180	18	1KHZ	90m	1.26	1.89
SCB75C-220	22	1KHZ	0.11	1.13	1.70
SCB75C-270	27	1KHZ	0.15	1.02	1.62
SCB75C-330	33	1KHZ	0.17	0.84	1.52
SCB75C-390	39	1KHZ	0.20	0.80	1.36
SCB75C-470	47	1KHZ	0.23	0.76	1.27
SCB75C-560	56	1KHZ	0.28	0.64	1.20
SCB75C-680	68	1KHZ	0.32	0.60	1.14
SCB75C-820	82	1KHZ	0.39	0.57	1.08
SCB75C-101	100	1KHZ	0.44	0.50	0.96
SCB75C-121	120	1KHZ	0.48	0.47	0.91
SCB75C-151	150	1KHZ	0.73	0.40	0.81
SCB75C-181	180	1KHZ	0.78	0.39	0.72
SCB75C-221	220	1KHZ	0.94	0.33	0.64
SCB75C-271	270	1KHZ	1.25	0.31	0.58
SCB75C-331	330	1KHZ	1.40	0.27	0.49
SCB75C-391	390	1KHZ	1.52	0.27	0.44
SCB75C-471	470	1KHZ	1.90	0.25	0.42
SCB75C-561	560	1KHZ	2.39	0.22	0.40



- (1). Inductance tolerance for 1.0uH~6.8uH: $\pm 30\%$, for 10uH~560uH: $\pm 20\%$. Tested at 0.25V, 0ADC and 25°C
- (2). DCR measured at 25°C.
- (3). The DC current at which the inductance decreases by 10% from its initial value.
- (4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

© 2019 Signal Transformer – Specification subject to change without notice. 12.19



belfuse.com/signal

128 Atlantic Avenue, Lynbrook, NY 11563
Toll Free 866-239-5777 • Tel 516-239-5777 • Fax 516-239-7208
Sales@signaltransformer.com • techhelp@signaltransformer.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bel:](#)

SCB75C-6R8	SCB75C-1R0	SCB75C-181	SCB75C-470	SCB75C-101	SCB75C-270	SCB75C-120	SCB75C-271
SCB75C-680	SCB75C-330	SCB75C-560	SCB75C-121	SCB75C-471	SCB75C-390	SCB75C-151	SCB75C-220
SCB75C-180	SCB75C-820	SCB75C-331	SCB75C-391	SCB75C-561	SCB75C-100	SCB75C-3R3	SCB75C-221
SCB75C-4R7	SCB75C-150	SCB75C-1R5	SCB75C-2R2				