


SCRH124

SMD POWER INDUCTORS





• Features

1. Magnetically shielded construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (3) (A)	Temperature Current (4) (A)
SCRH124-3R9	3.9	100KHZ	15m	6.5	6.0
SCRH124-4R7	4.7	100KHZ	18m	5.7	5.4
SCRH124-6R8	6.8	100KHZ	23m	4.9	4.8
SCRH124-8R2	8.2	100KHZ	26m	4.6	4.4
SCRH124-100	10	100KHZ	28m	4.5	4.1
SCRH124-120	12	100KHZ	38m	4.0	3.9
SCRH124-150	15	100KHZ	50m	3.2	3.5
SCRH124-180	18	100KHZ	57m	3.1	3.1
SCRH124-220	22	100KHZ	66m	2.9	3.0
SCRH124-270	27	100KHZ	80m	2.8	2.7
SCRH124-330	33	100KHZ	97m	2.7	2.43
SCRH124-390	39	100KHZ	132m	2.1	2.07
SCRH124-470	47	100KHZ	160m	1.9	1.87
SCRH124-560	56	100KHZ	190m	1.8	1.77
SCRH124-680	68	100KHZ	220m	1.5	1.60
SCRH124-820	82	100KHZ	260m	1.3	1.44
SCRH124-101	100	100KHZ	308m	1.2	1.36
SCRH124-121	120	100KHZ	380m	1.1	1.23
SCRH124-151	150	100KHZ	530m	0.95	1.16
SCRH124-181	180	100KHZ	620m	0.85	1.05
SCRH124-221	220	100KHZ	700m	0.80	0.95
SCRH124-271	270	100KHZ	870m	0.60	0.86
SCRH124-331	330	100KHZ	990m	0.50	0.78



(1). Inductance tolerance for 3.9uH~8.2uH: $\pm 30\%$, for 10uH~330uH: $\pm 20\%$. Tested at 0.25V, 0ADC and 25°C

(2). DCR measured at 25°C.

(3). The DC current at which the inductance decreases by 25% from its initial value.

(4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

© 2019 Signal Transformer – Specification subject to change without notice. 12.19



belfuse.com/signal

128 Atlantic Avenue, Lynbrook, NY 11563
Toll Free 866-239-5777 • Tel 516-239-5777 • Fax 516-239-7208
Sales@signaltransformer.com • techhelp@signaltransformer.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SCRH124-150](#) [SCRH124-120](#) [SCRH124-820](#) [SCRH124-331](#) [SCRH124-470](#) [SCRH124-101](#) [SCRH124-220](#)
[SCRH124-680](#) [SCRH124-271](#) [SCRH124-270](#) [SCRH124-560](#) [SCRH124-330](#) [SCRH124-8R2](#) [SCRH124-4R7](#)
[SCRH124-6R8](#) [SCRH124-221](#) [SCRH124-3R9](#) [SCRH124-100](#) [SCRH124-390](#) [SCRH124-121](#) [SCRH124-181](#)
[SCRH124-151](#) [SCRH124-180](#)