

SMA 45° Connector

RF Solutions

The Johnson™ 45° PCB Mount SMA Connector is designed to offer mid-board launch in tight enclosures as well as board to board applications, where there may be height restrictions for vertical mount and width restrictions for an end launch connector.

Features



- Performance up to 18 GHz
- Maximum VSWR of 1.30 GHz to 12 GHz; 1.50 from 12 GHz to 18 GHz

Applications

- Semiconductor foundry equipment
- Instrumentation test fixture equipment
- Semi-conductor Testing
- Board characterization
- Test and measurement systems

SMA 45° Connectors

Part Number	Description	Material
142-0711-271	SMA Jack, 45 Degree PCB Mount	Beryllium Copper, Gold-Plated



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[142-0711-271](#)