

# Multi Axis Punch Down Plugs

## Cat6 and Cat6a Ethernet Solutions

Stewart Connector's Multi Axis Punch Down Plugs offer time saving solutions for unique Ethernet connections that require field terminations. These plugs have a termination option with a top, bottom or side entry.

## Features & Benefits

- The Multi Axis Punch Down Plugs are designed for quick and easy field terminations
- The Cat6 punch down plug is suitable for use in 1G Base-T networks and the Cat6a for 10G Base-T networks
- Contact designed for use on solid or stranded conductor cable
- 50 micro-inches of gold plating on contacts for increased cycle life
- Easy to use color coded conductor pre-load wire manager
- Terminates 22-26 AWG cable with a diameter over the insulation of up to 1.6mm (.063in)
- Accepts an overall cable OD of 6mm (.236in) to 8mm (.315in)
- IP20 rated

## Applications

- Suitable for both shielded and unshielded applications
- Compression strain relief
- No termination tooling required
- Adequate for Power Over Ethernet applications
- Utilizes robust zinc die-cast housings and latch protectors
- Each plug kits includes termination instructions

## Part Numbers

Part Number	Lan Category	Wire Gauge	Cable OD	
			in	mm
SS-39300-003	Cat6	22-26 AWG	.236-.315in	6-8mm
SS-39300-004	Cat6a	22-26 AWG	.236-.315in	6-8mm



**Stewart Connector**  
11118 Susquehanna Trail South  
Glen Rock, PA 17327-9199

+1 717.235.7512  
techhelp@belf.com  
[belfuse.com/stewart-connector](http://belfuse.com/stewart-connector)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SS-39300-003](#) [SS-39300-004](#)