

RED INDICATES ORIGINAL

DWG
SIZE
C


DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS, INC.
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR REPRODUCTION OR MANUFACTURE WITHOUT
EXPRESS WRITTEN PERMISSION.

| REVISIONS | | | 3-0207 | SH 1 |
|-----------|-------|---|--------|------------------|
| REV | EO | DESCRIPTION | DWN | APPROVED |
| M | 12085 | -308 TAI-218 WAS TAI-168; ADDED -308 & -309; SEE ECO | DKC | KLM (21) 8/26/97 |

| DASH NO | CABLES ACCOMMODATED | A HEX | B DIM | C MAX | ASSEMBLE PER |
|------------|------------------------|----------|----------|----------|-----------------|
| -201 | M17/176-00002 | .344 | .030 | 1.80 | TAI-168 |
| -202 | TWC-78-1 | | | | |
| -203 | TWC-124-1A | | | | |
| -204 | 10602, RAYCHEM | | | | |
| -205 | TVAC-78-1F2 | | | | |
| -206 | 782800130, RAYCHEM | | | | |
| -207 | 83310, BELDEN | | | | |
| -208 | 202-3927, MICRODOT | | | | |
| -209 | 202-3942, MICRODOT | | | | |
| -210 | 8451, BELDEN | | | | |
| -211 | 202-3934, MICRODOT | | | | |
| -212 | 2524E0114, RAYCHEM | | | | |
| -213 | TWC-78-2 | | | 1.55 | TAI-138 |
| -214 | TWC-124-2 | | | | |
| -215 | BL982, TIMES | | | | |
| -216 | BL 1242, TIMES | | | | |
| -217 | GC875TH24H, GRUMMAN | | | | |
| -218 | EDP221888, RAYCHEM | | | 1.80 | TAI-168 |
| -219 | 252801114, RAYCHEM | | | | |
| -220 | GC875RR1, GRUMMAN | | | | |
| -221 | 10614, RAYCHEM | | | | |
| -222 | 10613, RAYCHEM | | | | |
| -223 | HMS2-1149, HUGHES | | | | |

| DASH NO | CABLES ACCOMMODATED | A HEX | B DIM | C MAX | ASSEMBLE PER |
|------------|---------------------------|----------|----------|----------|-----------------|
| -301 | GC875GC1, GRUMMAN | .344 | .030 | 1.80 | TAI-168 |
| -302 | GC875GB1, GRUMMAN | | | | |
| -303 | 7528A5314, RAYCHEM | | | | |
| -304 | | | | | |
| -305 | M17/177-00001, THERMATICS | | | | TAI-218 |
| -306 | TRC-50-2 | | | | |
| -307 | M17/134-00002 | | | | TAI-168 |
| -308 | TRC-75-1 | | | | TAI-218 |
| -309 | TRC-75-2 | | | | TAI-168 |
| -309 | TRC-50-1 | | | | |

| INCH | MM |
|-------|-------|
| .005 | 0.13 |
| .010 | 0.25 |
| .030 | 0.76 |
| .106 | 2.77 |
| .218 | 5.54 |
| .221 | 5.61 |
| .344 | 8.74 |
| .505 | 12.83 |
| .510 | 12.95 |
| .625 | 15.88 |
| .687 | 17.45 |
| 1.00 | 25.40 |
| 1.25 | 31.75 |
| 1.416 | 35.97 |
| 1.55 | 39.37 |
| 1.75 | 44.45 |
| 1.80 | 45.72 |




-202 SHOWN

- 1 SHRINKABLE STRAIN RELIEF AND/OR SHRINKABLE SEALING SLEEVE SUPPLIED LOOSE AS FOLLOWS:
- CABLE GROUPS -201 THROUGH -210, -217 THROUGH -303, -305, -307 & -309
 - 1 SHRINKABLE STRAIN RELIEF (1.00 LONG)
 - 1 SHRINKABLE SEALING SLEEVE (1.25 LONG)
 - CABLE GROUPS -211 THROUGH -216, -306 & -308
 - 1 SHRINKABLE STRAIN RELIEF (1.75 LONG)
4. MAX PANEL THK .109
3. 4-LUG CONCENTRIC TWINAX/TRIAX TRB, FULL CRIMP BULKHEAD MOUNT CABLE RECEPTACLE
2. FINISH: TFS-1A (NICKEL)
1. ALL DIMENSIONS ARE IN INCHES

6. EXAMPLE OF COMPLETE MODEL NO:
BJ79CFL-201

BASIC MODEL NO _____ CABLE GROUP DASH NO _____



| QTY | DESCRIPTION | PART NUMBER | ITEM |
|--|--|---------------|--------------|
| TOL UNLESS SPECIFIED .001 ± .002 ± .003 ± .004 ± ANGLES ± | TROMPETER ELECTRONICS, INC. | BJ79CFL | |
| DWN | DKC | 8-1-87 | MATERIAL |
| CHK | KLM | 8-18-97 | CODE IDENT |
| ENGR | | | DRAWING NO. |
| APPR | | | 3-0207 |
| NEXT ASSY | SCALE 4/1 | DATE 11/11/98 | SHEET 1 OF 2 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[BJ79CFL-201](#)