

Specification Sheet

Part Number: T30RA3000



The AT2060 cable tie system is designed for automatic installation on bundles up to 1.25" and a minimum tensile strength of 30 lbs.

Available in reels of 3,000 each or bandoliers of 30 each.

Article Number	103-00001
Type	T30RA
Color	Natural (NA)
Quantity Per	pack
Product Description	Cable ties for use with HellermannTyton's AT2060 automatic cable tie tool
Short Description	Cable Ties for AT2060, 30lb Tensile Strength, PA66, Natural, 3000/reel
Global Part Name	T30RA-PA66-NA

Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	135
Length L (Imperial)	6.0
Length L (Metric)	152.4
Identification Plate Position	none
Reel Diameter (Imperial)	17.7
Reel Diameter (Metric))	450.0
Reel Width (Imperial)	7.197
Reel Width (Metric)	182.8
Voltage Range	27 Volt
Releasable Closure	No
Variant	on reel
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.25

Bundle Diameter Max (Metric)	31.75
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Cycle Time	1.2 seconds
Tension Setting Tools	Adjustable
Power Supply	Electrical
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CAGE Code 53421 UL-ZODZ2.E64139

UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988
Reel Weight (Imperial)	7
Reel Weight (Metric)	3.175

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T30RA3000](#)