

Specification Sheet

Part Number: 111-01569



Inside serrations allow for strong grip on cables and wire bundles

Head design provides high tensile strength with very low insertion force

Cable Tie, 8" Long, 50lb Tensile Strength, POMUV, Black, 1000/pkg

Article Number	111-01569
Type	T50R
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton Standard Cable Ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 8" Long, 50lb Tensile Strength, POMUV, Black, 1000/pkg
Global Part Name	T50R-POMUV-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.95
Length L (Metric)	202.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.1
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2

Cable Tie Head Length (Imperial)	0.29
Cable Tie Head Width (Imperial)	0.3
Material	Polyacetal, UV stabilized (POMUV)
Material Shortcut	POMUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[111-01569](#)