

Specification Sheet

Part Number: T120S0HSH4



Heat stabilized heavy duty cable ties provide excellent resistance to high heat exposures.

Head design provides high tensile strength with very low insertion force.

Heavy Duty Cable Tie, 9" Long, UL Rated, 120lb Tensile Strength, PA66HS, Black, 500/pkg

|                     |                                                                                                                                                                                                                                                                                                         |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 111-12821                                                                                                                                                                                                                                                                                               |
| Type                | T120S                                                                                                                                                                                                                                                                                                   |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                              |
| Quantity Per        | bag                                                                                                                                                                                                                                                                                                     |
| Product Description | Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. |
| Short Description   | Heavy Duty Cable Tie, 9" Long, UL Rated, 120lb Tensile Strength, PA66HS, Black, 500/pkg                                                                                                                                                                                                                 |
| Global Part Name    | T120S-PA66HS-BK                                                                                                                                                                                                                                                                                         |

|                                     |                 |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 120             |
| Minimum Tensile Strength (Metric)   | 535             |
| Length L (Imperial)                 | 9.0             |
| Length L (Metric)                   | 225.0           |
| Identification Plate Position       | none            |
| Releasable Closure                  | No              |
| Tie Closure                         | plastic pawl    |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.30            |
| Width W (Metric)                    | 7.6             |
| Bundle Diameter Min (Imperial)      | 0.2             |
| Bundle Diameter Min (Metric)        | 5.0             |
| Bundle Diameter Max (Imperial)      | 2.17            |
| Bundle Diameter Max (Metric)        | 55.0            |
| Thickness T (Metric)                | 1.6             |
| Cable Tie Head Length (Imperial)    | 0.39            |

|                                 |                                        |
|---------------------------------|----------------------------------------|
| Cable Tie Head Width (Imperial) | 0.52                                   |
| Height H (Metric)               | 7.7                                    |
| Material                        | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut               | PA66HS                                 |
| Flammability                    | UL 94 V-2                              |
| Halogen Free                    | Yes                                    |
| UV Resistant (Yes/No)           | No                                     |
| Use Conditions                  | For Indoor and Outdoor Use             |
| Plenum Rating                   | AH-2                                   |
| Operating Temperature           | -40°F to +257°F (-40°C to +125°C)      |
| Reach Compliant (Article 33)    | Yes                                    |
| ROHS Compliant                  | Yes                                    |
| Certification/Specification     | UL 62275                               |
| UL Recognized (US)              | Yes                                    |
| UL Listed (US and Canada)       | Yes                                    |

|                               |            |
|-------------------------------|------------|
| UL Recognized (US and Canada) | Yes        |
| UL Listed (US)                | Yes        |
| Package Quantity (Imperial)   | 500        |
| Package Quantity (Metric)     | 500        |
| Customs Number                | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T120S0HSH4](#)