


Specification Sheet

Part Number: T150L0C2



Engineered and manufactured for maximum performance and quality.

Made from 100% high-quality plastic to ensure efficient recycling.

Inside serration for a strong grip onto bundles.

Easy application either manually or with a tensioning tool.

Heavy Duty Cable Tie, 32" Long, UL Rated, 175lb Tensile Strength, PA66, Black, 100/pkg

Article Number	111-15402
----------------	-----------

Type	T150L
------	-------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	---

Short Description	Heavy Duty Cable Tie, 32" Long, UL Rated, 175lb Tensile Strength, PA66, Black, 100/pkg
-------------------	--

Global Part Name	T150L-PA66-BK
------------------	---------------

Minimum Tensile Strength (Imperial)	175.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	780
-----------------------------------	-----

Length L (Imperial)	32.0
---------------------	------

Length L (Metric)	820.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.35
--------------------	------

Width W (Metric)	8.9
------------------	-----

Bundle Diameter Min (Imperial)	0.31
--------------------------------	------

Bundle Diameter Min (Metric)	8.0
------------------------------	-----

Bundle Diameter Max (Imperial)	9.65
--------------------------------	------

Bundle Diameter Max (Metric)	245.0
------------------------------	-------

Thickness T (Metric)	1.9
----------------------	-----

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Plenum Rating	AH-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100

Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T150L0C2](#)