

Specification Sheet

Part Number: 111-85850



An all-in-one bundling and fixing solution reduces costs.

Disc provides secure insertion and minimizes access of dust, dirt and water.

1-Piece Cable Tie with Arrowhead Mount, 8.9"L, 50lb, Mounting Hole Dia. 0.27 - 0.28", PA66HS, Black, 100/pkg

Article Number	111-85850
----------------	-----------

Type	T50MD7
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pcs.
--------------	------

Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
---------------------	--

Short Description	1-Piece Cable Tie with Arrowhead Mount, 8.9"L, 50lb, Mounting Hole Dia. 0.27 - 0.28", PA66HS, Black, 100/pkg
-------------------	--

Global Part Name	T50MD7-PA66HS-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.0
Length L (Metric)	225.0
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.20
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	2.32
Bundle Diameter Max (Metric)	59.0
Thickness T (Imperial)	0.06

Thickness T (Metric)	1.5
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	1.2
Panel Thickness Max (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.27 - 0.28
Mounting Hole Diameter D (Metric)	6.8 - 7.2 mm
Mounting Hole Diameter D Min (Imperial)	0.27
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.2
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[111-85850](#)