

Specification Sheet

Part Number: 117-00008



Heat stabilized cable ties provide excellent resistance to high heat exposures

Head design contains clamping rails to provide full circumferential compression around bundles

Bent tail allows for quick insertion into head

Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66HS, Black, 100/pkg

Article Number	117-00008
Type	T50LDH
Color	Black (BK)
Quantity Per	bag
Product Description	The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Double-Head Cable Tie, 15.6" Long, 50lb Tensile Strength, PA66HS, Black, 100/pkg

Global Part Name	T50LDH-PA66HS-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	15.6
---------------------	------

Length L (Metric)	395.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	3.94
--------------------------------	------

Bundle Diameter Max (Metric)	100
------------------------------	-----

Bundle Diameter 1st Loop Max (Imperial)	4.0
---	-----

Bundle Diameter 2nd Loop Max (Imperial) 2.0

Thickness T (Imperial) 0.055

Thickness T (Metric) 1.4

Cable Tie Head Length (Imperial) 0.53

Cable Tie Head Width (Imperial) 0.32

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

Halogen Free Yes

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +257°F (-40°C to +125°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Certification/Specification UL | ANSI/UL 62275 UL | ANSI/UL 746B UL | ANSI/UL 1565

UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[117-00008](#)