

Specification Sheet

Part Number: 126-00074



Wing design helps stabilize the tie in high-vibration applications. Includes a ladder-type strap as opposed to a conventional serrated strap which provides the benefit of being extra flexible.

Tie is releasable and reusable giving additional use options.

1-Pc Cable Tie/Arrowhead Mount w/Wings, 8"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HS, Black, 100/bag

Article Number	126-00074
----------------	-----------

Type	T50RSFM
------	---------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
---------------------	--

Short Description	1-Pc Cable Tie/Arrowhead Mount w/Wings, 8"L, 50lb, 0.24 - 0.26" Hole Dia, PA66HS, Black, 100/bag
-------------------	--

Global Part Name	T50RSFM-PA66HS-BK
-------------------------	-------------------

Minimum Tensile Strength (Imperial)	50.0
--	------

Minimum Tensile Strength (Metric)	225.0
--	-------

Length L (Imperial)	8.0
----------------------------	-----

Length L (Metric)	203.2
--------------------------	-------

Fixation Method	Arrowhead
------------------------	-----------

Identification Plate Position	none
--------------------------------------	------

Releasable Closure	No
---------------------------	----

Tie Closure	plastic pawl
--------------------	--------------

Variant	Inside Serrated
----------------	-----------------

Width W (Imperial)	0.18
---------------------------	------

Width W (Metric)	4.6
-------------------------	-----

Bundle Diameter Min (Imperial)	0.06
---------------------------------------	------

Bundle Diameter Min (Metric)	1.5
-------------------------------------	-----

Bundle Diameter Max (Imperial)	1.77
---------------------------------------	------

Bundle Diameter Max (Metric)	45.0
-------------------------------------	------

Thickness T (Metric)	1.3
Height H (Imperial)	0.22
Height H (Metric)	5.6
Panel Thickness Min (Imperial)	0.028
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 -0.26
Mounting Hole Diameter D (Metric)	6.0 - 6.6 mm
Mounting Hole Diameter D Max (Metric)	6.6

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
ROHS Compliant	Yes

Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[126-00074](#)