

Specification Sheet

Part Number: 126-00080



Design helps silence and stabilize the tie in high-vibration applications. Arrowhead-style mount provides low insertion and high extraction force. Anti-rotational oval fastener forces bundle to travel in intended direction. Rubber seal restricts water and debris from passing through mounting hole.

Article Number	126-00080
Type	T60SOSSFT62x122-E-MD
Color	Black (BK)
Quantity Per	bag
Product Description	Push Mount Ties with Seal for Oval Holes provide a one-piece bundling and mounting solution. The oval arrowhead fastener won't rotate once inserted into a panel hole, ensuring proper routing of wires and hoses. The welded rubber seal protects against the ingress of water and debris.
Short Description	Push Mount Tie with Seal, 6.2" Long, Mounting Hole Diameter 0.24"-0.48", PA66HS, Black, 500/pkg
Global Part Name	T60SOSSFT62x122-E-MD-PA66HS-BK

Minimum Tensile Strength (Imperial)	67.0
Minimum Tensile Strength (Metric)	300
Length L (Imperial)	6.2
Length L (Metric)	157.5
Fixation Method	Arrowhead for oval holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.22
Width W (Metric)	5.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30.0
Thickness T (Metric)	1.35

Panel Thickness Min (Imperial)	0.023
Panel Thickness Max (Imperial)	0.079
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.48
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.48
Mounting Hole Diameter D Max (Metric)	12.2
Disc Diameter (Metric)	16.0 x 22.0
Disc Diameter (Imperial)	0.63

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[126-00080](#)