

Specification Sheet

Part Number: 126-00326



All-in-one bundling and mounting solution reduces costs.
Low-profile design provides dependable cable management in tight spaces.

1-Pc Cable Tie/Arrowhead Mount w/Disc, 6.2"L, 0.25" - 0.26" Hole Dia, PA66HS, Black, 500/pkg

Article Number	126-00326
-----------------------	-----------

Type	T50SOSKSFT6.5S2-E
-------------	-------------------

Color	Black (BK)
--------------	------------

Quantity Per	bag
---------------------	-----

Product Description	HellermannTyton's low profile push mount design provides an overall shortened length which assists in limiting protrusion on the opposing side of application surfaces. The rounded tip of the mount allows for a smoother surface in case of contact with surrounding components or human touch during service.
----------------------------	--

Short Description	1-Pc Cable Tie/Arrowhead Mount w/Disc, 6.2"L, 0.25" - 0.26" Hole Dia, PA66HS, Black, 500/pkg
--------------------------	--

Global Part Name	T50SOSKSFT6.5S2-E-PA66HS-BK
------------------	-----------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225.0
-----------------------------------	-------

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	157.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.04
--------------------------------	------

Bundle Diameter Min (Metric)	1.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Height H (Imperial)	0.58
Height H (Metric)	14.732
Panel Thickness Min (Imperial)	0.07
Panel Thickness Max (Imperial)	0.09
Panel Thickness Min (Metric)	1.7
Panel Thickness Max (Metric)	2.3
Mounting Hole Diameter D (Imperial)	0.25 - 0.26
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63

Material	Polyamide 6.6 heat stabilized (PA66HS)
-----------------	--

Material Shortcut	PA66HS
--------------------------	--------

Flammability	UL 94 V-2
---------------------	-----------

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
------------------------------	-----------------------------------

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	500
------------------------------------	-----

Package Quantity (Metric)	500
----------------------------------	-----

Customs Number	3926909988
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[126-00326](#)