

Specification Sheet

Part Number: T18RWPM9M4

Easy and quick insertion ideal for production environment.

Tie "clicks" into place upon final installation signaling installer insertion is complete.

Arrowhead style mount provides low insertion and high extraction force.



1-Piece Cable Tie/Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66, Natural, 1000/pkg

Article Number	126-00603
----------------	-----------

Type	T18RWPM
------	---------

Color	Natural (NA)
-------	--------------

Quantity Per	bag
--------------	-----

Product Description	Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
---------------------	--

Short Description	1-Piece Cable Tie/Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66, Natural, 1000/pkg
-------------------	---

Global Part Name	T18RWPM-PA66-NA
------------------	-----------------

Minimum Tensile Strength (Imperial)	18
-------------------------------------	----

Minimum Tensile Strength (Metric)	80
-----------------------------------	----

Length L (Imperial)	4.5
---------------------	-----

Length L (Metric)	113.0
-------------------	-------

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.1
--------------------	-----

Width W (Metric)	2.5
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	0.87
--------------------------------	------

Bundle Diameter Max (Metric)	22.0
------------------------------	------

Thickness T (Imperial)	0.043
Thickness T (Metric)	1.1
Height H (Imperial)	.23
Height H (Metric)	5.80
Panel Thickness Min (Imperial)	0.06
Panel Thickness Max (Imperial)	0.13
Panel Thickness Min (Metric)	1.52
Panel Thickness Max (Metric)	3.2
Mounting Hole Diameter D (Imperial)	0.19 - 0.22
Mounting Hole Diameter D (Metric)	4.8 - 5.6 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.22
Mounting Hole Diameter D Max (Metric)	5.6
Disc Diameter (Metric)	13.1
Disc Diameter (Imperial)	0.5

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T18RWPM9M4](#)