

Specification Sheet

Part Number: RT250M0UVX2



UV stabilized heavy duty cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.

Special design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Buckle feature on head allows excess strap to be tucked away after installation.

Releasable Cable Tie, Release Tab, 22.3" Long, 250lb Tensile Strength, PA66UV, Black, 25/pkg

Article Number	131-75620
Type	RT250M
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton heavy-duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Releasable Cable Tie, Release Tab, 22.3" Long, 250lb Tensile Strength, PA66UV, Black, 25/pkg
Global Part Name	RT250M-PA66UV-BK
Minimum Tensile Strength (Imperial)	250
Minimum Tensile Strength (Metric)	1115
Length L (Imperial)	22.3
Length L (Metric)	565.3
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.49
Width W (Metric)	12.5
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	5.91

Bundle Diameter Max (Metric)	150.0
Thickness T (Imperial)	0.075
Thickness T (Metric)	1.9
Cable Tie Head Length (Imperial)	0.88
Cable Tie Head Width (Imperial)	0.79
Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
Flammability	UL 94 V-2
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 746B UL ANSI/UL 1565 UL ANSI/UL 62275
UL Recognized (US)	Yes

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[RT250M0UVX2](#)