

Specification Sheet

Part Number: 133-00285



Tubes are fixed a defined distance from the substructure.

Defined diameter for the wire entry.

Retainer is fixed in the hole with BHT-tie.

Cable Guide Standoff, 1.0" Max Bundle Diameter, PA66HIRHS, Black, 150/pkg

Article Number 133-00285

Type CGS2

Color Black (BK)

Quantity Per carton

Product Description This cable guide standoff is designed for the use with HellermannTyton's button head ties. The cable guide standoff stands off bundles from frame rails, providing clearance from bolts and other protrusions for protection against abrasion. This mount also allows the flow-through of salt, dirt and other impurities from the road, preventing unwanted build-up on hoses and harnesses. This product perfectly secures convoluted tubing's up to 26mm in diameter.

Short Description Cable Guide Standoff, 1.0" Max Bundle Diameter, PA66HIRHS, Black, 150/pkg

Global Part Name	CGS2-PA66HIRHS-BK
Length L (Imperial)	3.23
Length L (Metric)	82.04
Variant	Mounts
Width W (Imperial)	1.5
Width W (Metric)	38.1
Bundle Diameter Max (Imperial)	1.02
Bundle Diameter Max (Metric)	25.9
Mounting Hole Diameter D (Imperial)	0.50
Mounting Hole Diameter D (Metric)	12.7 mm
Mounting Hole Diameter D Min (Imperial)	0.5
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Operating Temperature -40°F to +257°F (-40°C to +125°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 150

Package Quantity (Metric) 150

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-00285](#)