

Specification Sheet

Part Number: 133-00998



Separates and secures bundles avoiding abrasion.

Designed to handle both convoluted tubing and bundles not covered in convoluted tubing.

Available in a variety of sizes and colors to be easily identified.

HC Clamp Bundle Separator, Three Hole, PA66GFHIRHS, Black, 500/pkg

Article Number	133-00998
----------------	-----------

Type	HC3A
------	------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.
---------------------	--

Short Description	HC Clamp Bundle Separator, Three Hole, PA66GFHIRHS, Black, 500/pkg
-------------------	--

Global Part Name	HC3A-PA66HIRGF13-BK
------------------	---------------------

Length L (Imperial)	4.246
---------------------	-------

Length L (Metric)	107.86
-------------------	--------

Variant	Separators
---------	------------

Width W (Imperial)	1.1
--------------------	-----

Width W (Metric)	27.94
------------------	-------

Bundle Diameter Min (Imperial)	0.96
--------------------------------	------

Bundle Diameter Min (Metric)	24.39
------------------------------	-------

Bundle Diameter Max (Imperial)	0.96
--------------------------------	------

Bundle Diameter Max (Metric)	24.3
------------------------------	------

Bundle Diameter 1st Loop Max (Imperial)	0.96
---	------

Bundle Diameter 1st Loop Max (Metric)	24.39
---------------------------------------	-------

Bundle Diameter 2nd Loop Max (Imperial)	0.96
---	------

Bundle Diameter 2nd Loop Max (Metric)	24.39
---------------------------------------	-------

Height H (Imperial)	1.38
---------------------	------

Height H (Metric)	34.94
-------------------	-------

Mounting Hole Diameter D (Imperial)	0.32
Mounting Hole Diameter D (Metric)	8.12 mm
Material	Polyamide 6.6, high impact modified, glass-fiber reinforced (PA66HIRGF13)
Material Shortcut	PA66HIRGF13
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-00998](#)