

Specification Sheet

Part Number: 133-01480



- Angled channel provides specific guidance around corners or obstructions.
- Mounting holes for cable ties allow for easy bundling.
- Polypropylene material provides good chemical and heat resistance.
- Design protects bundles against abrasion and other environmental factors.

Mini Channel, 2.05" Long, 45° Angle, Small, PPT20, Black, 4000/pkg

Article Number	133-01480
Type	45MINICHNL
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.
Short Description	Mini Channel, 2.05" Long, 45° Angle, Small, PPT20, Black, 4000/pkg
Global Part Name	45MINICHNL-PPTD20-BK

Length L (Imperial)	2.05
Length L (Metric)	52.0
Variant	135°
Width W (Imperial)	0.06
Width W (Metric)	10.0
Height H (Imperial)	0.39
Height H (Metric)	10.0
Material	Polypropylene 20% Talkum (PPTD20)
Material Shortcut	PPTD20
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-01480](#)