

Specification Sheet

Part Number: 133-03391



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple configurations to mount to a variety of surfaces

Releaseable to allow for maintenance

Conduit Clamps, Size 13, Mounting Hole 8.8 mm, Offset 38.2 mm, PA66, Black, 350/carton

Article Number	133-03391
----------------	-----------

Type	CDC13B45OS21.3M8
------	------------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters.
---------------------	---

Short Description	Conduit Clamps, Size 13, Mounting Hole 8.8 mm, Offset 38.2 mm, PA66, Black, 350/carton
-------------------	--

Global Part Name	CDC13B45OS21.3M8-PA66-BK
-------------------------	--------------------------

Length L (Imperial)	2.44
----------------------------	------

Length L (Metric)	62.1
--------------------------	------

Offset Length (Imperial)	1.5
---------------------------------	-----

Offset Length (Metric)	38.2
-------------------------------	------

Fixation Method	screwable
------------------------	-----------

Width W (Imperial)	0.9
---------------------------	-----

Width W (Metric)	23
-------------------------	----

Bundle Diameter Max (Imperial)	0.51
---------------------------------------	------

Bundle Diameter Max (Metric)	13.0
-------------------------------------	------

Height H (Imperial)	2.58
----------------------------	------

Height H (Metric)	65.6
--------------------------	------

Diameter D (Imperial)	0.55
------------------------------	------

Diameter D (Metric)	14.0
----------------------------	------

Mounting Hole Diameter D (Imperial)	0.35
--	------

Mounting Hole Diameter D (Metric)	8.8 mm
--	--------

Stud Diameter (Metric)	M8
Stud Diameter (Imperial)	M8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	350
Package Quantity (Metric)	350
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-03391](#)