

Specification Sheet

Part Number: 133-03431



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple configurations to mount to a variety of surfaces

Releaseable to allow for maintenance

Conduit Clamps, Size 13, Mounting Hole 10.6 mm, Offset, 28.1 mm, PA66, Black, 900/carton

Article Number	133-03431
----------------	-----------

Type	CDC13B90OS26.2M10
------	-------------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters.
---------------------	---

Short Description	Conduit Clamps, Size 13, Mounting Hole 10.6 mm, Offset, 28.1 mm, PA66, Black, 900/carton
-------------------	--

Global Part Name	CDC13B90OS26.2M10-PA66-BK
-------------------------	---------------------------

Length L (Imperial)	1.9
----------------------------	-----

Length L (Metric)	48.2
--------------------------	------

Offset Length (Imperial)	1.11
---------------------------------	------

Offset Length (Metric)	28.1
-------------------------------	------

Fixation Method	screwable
------------------------	-----------

Width W (Imperial)	0.9
---------------------------	-----

Width W (Metric)	23
-------------------------	----

Bundle Diameter Max (Imperial)	0.51
---------------------------------------	------

Bundle Diameter Max (Metric)	13.0
-------------------------------------	------

Height H (Imperial)	2.98
----------------------------	------

Height H (Metric)	75.8
--------------------------	------

Diameter D (Imperial)	0.55
------------------------------	------

Diameter D (Metric)	14.0
----------------------------	------

Mounting Hole Diameter D (Imperial)	0.42
--	------

Mounting Hole Diameter D (Metric)	10.6 mm
--	---------

Stud Diameter (Metric)	M10
Stud Diameter (Imperial)	M10
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	900
Package Quantity (Metric)	900
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-03431](#)