

Specification Sheet

Part Number: 133-03524



The different fastening orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters

Edge Clip and Tape Clip, Panel Thickness .03" - .08", 1.43" Long, PA66HIRHSUV, Black, 4000/ctn

Article Number	133-03524
Type	TEC50
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton’s edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
Short Description	Edge Clip and Tape Clip, Panel Thickness .03" - .08", 1.43" Long, PA66HIRHSUV, Black, 4000/ctn

Global Part Name	TEC50-PA66HIRHSUV/MET-BK
-------------------------	--------------------------

Length L (Imperial)	0.59
----------------------------	------

Length L (Metric)	15.1
--------------------------	------

Offset Length (Imperial)	0.36
---------------------------------	------

Offset Length (Metric)	9.2
-------------------------------	-----

Width W (Imperial)	0.39
---------------------------	------

Width W (Metric)	9.9
-------------------------	-----

Bundle Diameter Max (Imperial)	0.16
---------------------------------------	------

Bundle Diameter Max (Metric)	7.8
-------------------------------------	-----

Height H (Imperial)	0.3
----------------------------	-----

Height H (Metric)	7.5
--------------------------	-----

Diameter D (Imperial)	0.16
------------------------------	------

Diameter D (Metric)	4.0
----------------------------	-----

Panel Thickness Min (Imperial)	0.03
---------------------------------------	------

Panel Thickness Max (Imperial)	0.08
---------------------------------------	------

Panel Thickness Min (Metric)	0.8
-------------------------------------	-----

Panel Thickness Max (Metric)	2.0		
Material	Metal (MET) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)		
Material Shortcut	PA66HIRHSUV MET		
ROHS Compliant	Yes		
Package Quantity (Imperial)	4000		
Package Quantity (Metric)	4000		
Customs Number	3926909988		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-03524](#)