

Specification Sheet

Part Number: 148-90048

Spring technology for safe, secure and reliable connections.

Smaller footprint fits in tight spaces.

Low insertion force makes installation of solid or stranded copper wire fast and easy.

Color coded for easy identification of size.

Each port accepts multiple wire diameters for flexible applications.

Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire.



HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 2-Port, (PC), Yellow, 500/pkg

Article Number	148-90048
----------------	-----------

Type	HCPM-2
------	--------

Color	Yellow (YE) Clear (CL)
-------	------------------------

Quantity Per	pack
--------------	------

Product Description	HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal spring technology is approved for solid and stranded wires.
---------------------	---

Short Description	HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 2-Port, (PC), Yellow, 500/pkg
Global Part Name	HCPM-2-PC-CL/YE
Length L (Imperial)	0.65
Length L (Metric)	16.5
Width W (Imperial)	0.42
Width W (Metric)	10.8
Height H (Imperial)	0.30
Height H (Metric)	7.70
Depth D (Imperial)	0.65
Depth D (Metric)	16.5
Material	Polycarbonate (PC)
Material Shortcut	PC
Flammability	UL 94 V-0
Halogen Free	Yes

UV Resistant (Yes/No)	No
Operating Temperature	-22°F to +185°F (-30°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	VDE DIN EN 60998-2-2:2005-03 NF EN 60695-2-11 (2014) NF EN 60695-2-10 (2013) UL ANSI/UL 486-B CE 2006/65/EC NEMKO AS EN 60998-2-2:2004 SGS Fimko Ltd EN 60998-2-2:201 Intertek Semko EN 60998-2-2:2004 ENEC SGS Fimko Ltd EN 60998-2-2:2004 UL ANSI/UL 486-C cULus UL ANSI/UL 486-A
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	8536908085

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[148-90048](#)