

Specification Sheet

Part Number: 150-37791



Two-piece assembly allows mount to slide along strap, ensuring proper orientation.
Arrowhead-style mount provides low insertion and high extraction force.
Multiple material options provide solutions for any environment.

2-Piece Cable Tie/Arrowhead Mount, 6.5mm hole dia., 0.6-8.25mm Panel Thickness, PA66HIRHS, Black, 500/bag

Article Number	150-37791
Type	T50ROSSFT6.5-16-3
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton's Arrowhead Push Mount Tie Assembly is a two piece design allowing the mount to slide along the strap of the tie to ensure proper orientation. The arrowhead mount is designed for low insertion into a pre-drilled hole, while providing a high extraction force. The disc also protects against dirt and other impurities.
Short Description	2-Piece Cable Tie/Arrowhead Mount, 6.5mm hole dia., 0.6-8.25mm Panel Thickness, PA66HIRHS, Black, 500/bag

Global Part Name	T50ROSSFT6.5-16-3-PA66HS/PA66HIRHS-BK
------------------	---------------------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	7.87
---------------------	------

Length L (Metric)	200
-------------------	-----

Fixation Method	Arrowhead
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.181
--------------------	-------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.197
--------------------------------	-------

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.77
--------------------------------	------

Bundle Diameter Max (Metric)	45.0
------------------------------	------

Height H (Imperial)	0.051
---------------------	-------

Height H (Metric)	1.3
Panel Thickness Min (Imperial)	0.098
Panel Thickness Max (Imperial)	0.138
Panel Thickness Min (Metric)	2.5
Panel Thickness Max (Metric)	3.5
Mounting Hole Diameter D (Imperial)	0.248 - 0.264
Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
Mounting Hole Diameter D Min (Imperial)	0.248
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)

Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[150-37791](#)